


## 12038 【120x120x38 mm】



## AC Fan Series

### Dimensions Drawing



### Specifications

Model	Bearing Type	Rated Voltage	Frequency	Rated Current	Power Consumption	Speed Reference	Air Flow		Static Pressure		Noise	Weight
		VAC	Hz	AMP	Watts	RPM	m3/min	CFM	mmH2O	Inch-H2O		
EC12038A1HBX	Ball	115	60	0.16	10	2600	2.35	83	6.5	0.256	43	460
EC12038A1HSX	Sleeve											
EC12038A2HBX	Ball	220/240	50	0.11	18	2500	2.12	75	5.2	0.205	40	460
EC12038A2HSX	Sleeve											

- ▶ X mean : T-Terminal / L - Lead wire
- ▶ Frequency(Hz) : 50 / 60
- ▶ Insulation Resistance : AC 1500V-100MΩ
- ▶ Resist Strength : 1500V/min