



SIMATIC S7-300, Front connector with screw contacts, 40-pole

General information	
Product type designation	Front connector
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	60 °C
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Accessories	
belongs to product	S7-300
connection method	
Connection I/O signals	
• Connection method	Screw terminals
• Number of lines per connection	1; Or 2 cables up to 0.75 mm ² (total) in a shared end sleeve
Conductor cross-section in mm ²	
— Connectable cable cross-sections for massive cables, min.	0.14 mm ²
— Connectable cable cross-sections for massive cables, min.	0.75 mm ²
— Connectable cable cross-sections for flexible cables without end sleeve, min.	0.14 mm ²
— Connectable cable cross-sections for flexible cables without end sleeve, max.	0.75 mm ²
— Connectable cable cross-sections for flexible cables with end sleeve, min.	0.14 mm ²
— Connectable cable cross-sections for flexible cables with end sleeve, max.	0.75 mm ²
Conductor cross-section acc. to AWG	
— Connectable cable cross-sections for massive cables, min.	24
— Connectable cable cross-sections for massive cables, min.	19
— Connectable cable cross-sections for flexible cables without end sleeve, min.	24
— Connectable cable cross-sections for flexible cables without end sleeve, max.	19
— Connectable cable cross-sections for flexible cables with end sleeve, min.	24
— Connectable cable cross-sections for flexible cables with end sleeve, max.	19
Wire end processing	
— Stripped length of cables, min.	6 mm
— Stripped length of cables, max.	6 mm

- End sleeve acc. to DIN 46228 without plastic sleeve Design A, 5 mm to 7 mm long
- End sleeve acc. to DIN 46228 with plastic sleeve Design E, up to 6 mm long

Mounting

- Tool Screwdriver, conical design, 3 mm to 3.5 mm
- Tightening torque, min. 0.4 N·m
- Tightening torque, max. 0.7 N·m

Dimensions

Width	21.6 mm
Height	125 mm
Depth	40.9 mm

Weights

Weight, approx.	137 g
-----------------	-------

last modified:

8/27/2023 