

Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings

- PDF Copper Butt ..

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'SCS8-L'


Your search criteria matched only one product, shown below

SCS8-L



For Use with Stranded Copper Conductors

- Color-coded barrels marked with *PANDUIT* and specified competitor die index numbers for proper crimp die selection
- Internal wire stops to prevent over-insertion of conductor
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with *PANDUIT* and specified competitor crimping tools and dies
- UL Listed and CSA Certified for wide wire range -taking capability when crimped with *PANDUIT*® *Uni-Die*™ Dieless Crimping Tools‡
- **Tested by Telcordia – meets NEBS Level 3**
- American Bureau of Shipping Approved

Part Number	SCS8-L
RoHS Compliancy Status	Compliant
Part Description	Copper Butt Splice, standard barrel, #8 AWG wire.
Product Type	Compression Connectors- Splices
CSA Certified	Yes
UL Listed	Yes
Length (In.)	1.50
Length (mm)	38.1
Copper Conductor Size	#8 AWG
Barrel O.D.	.27
Barrel I.D.	.18
Panduit Color Code	Red
Panduit Die Index No.	P21
Pricing Description	Copper Compression Butt Splice, Standard Barrel, #8 AWG
Wire Strip Length (In.)	11/16
Min. Order UOM	PC
Min. Order Qty.	1
Burndy Die Index No.	49
T&B Die Index No.	21
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.