

Specifications

Items	Min	Norm	Max	Unit
Working Voltage	4.75	5.0	5.25	V
Switched Power	10			W
Switched Voltage AC,RMS value(max)	< 140			V
Switched Current DC	< 500			mA
Carry Current DC	< 0.5			A
Contact Resistance	<200			mΩ
Insulation Resistance	>10 ⁶			MΩ
Operating Temperature	-40	-	125	°C
Operate Range	10	-	40	AT