# **Micro-Fit Cable Assemblies**

# molex

Standard Micro-Fit TPA and non TPA Cable Assemblies deliver an off-the-shelf solution with a variety of cable lengths and a 3.00mm-pitch connector with a 6.5 to 8.5A maximum current rating to facilitate both prototyping and global production

## **Features and Advantages**

Multi-color cable configurations with Micro-Fit TPA and non TPA Receptacles available off the shelf

Designed to support development and production programs. Multi-color cables ensure correct connection



Available in single- and dual-row configurations

Dravidos design flevibility

Provides design flexibility

Micro-Fit TPA and non TPA Receptacles' 6.5 to 8.5A current rating and 3.00mm pitch

Delivers a high-density, lower power connection. Reduces terminal back-out



#### Assembled in ISO/TS16949certified facilities

Ensures high quality. Meets current automotive industry standards

## **Applications**

### Consumer / Home Appliance

Harness manufacturers

**Appliances** 

#### Data / Computing

Harness manufacturers

Desktops

Workstations

Power supplies

Uninterruptible Power Supply (UPS)

#### Telecommunications / Networking

Harness manufacturers

Servers

Routers

Switches

#### **Automotive / Commercial Vehicle**

Harness manufacturers

Non-sealed applications

Inside devices



Meets 2011/65/EU RoHS Compliance
Decreases engineering time and resources

UL 1007 discrete wires (TPA versions); UL1061 discrete wires (single-row; TPA versions); UL 1061 discrete wires (dual-row; non TPA versions)

Ready to use in electronic appliance applications. Provide ease of design, prototyping and production



Workstation



Refrigerator



Servers

# **Micro-Fit Cable Assemblies**



# **Specifications**

REFERENCE INFORMATION

Packaging:

UL File No.: E29179 CSA File No.: LR19980

Mates With:

Micro-Fit 3.0 Connectors Use With: Micro-Fit Headers Designed In: Millimeters

RoHS: Yes

Halogen Free: No, Low Halogen Glow Wire Compliant: No

**ELECTRICAL** 

Voltage (max.): 300V AC/DC Current (max.): 6.5 to 8.5A

**MECHANICAL** 

Contact Insertion Force (max.): 14.7N per contact Contact Retention to Housing (min.): 24.5N Mating Force (max.): 8N per circuit

Durability (max.):typically 30 cycles, refer to product

specifications

**PHYSICAL** 

Housing:

Panel Mount Ears

Receptacle: Black; without TPA Plug: Black; without TPA

Flammability: UL 94V-0

OL 94V-0

Operating Temperature:

Up to 105°C for TPA variant

Up to 80°C for non TPA variant

Up to 105°C for single row TPA variant

Plating:

Contact Area--Tin (1.02µm) and Gold (0.76µm)

# **Ordering Information**

| Series No.    | Product   | Circuits | Lengths (mm)              |
|---------------|---|----------|---------------------------|
| <u>45132</u>  | Off-the-Shelf Micro-Fit Dual-Row TPA Discrete Wire Cable Assemblies   | 4, 6, 8  | 150.00, 300.00 and 600.00 |
| <u>145132</u> | Off-the-Shelf Micro-Fit Single-Row TPA Discrete Wire Cable Assemblies | 2 to 7   | 150.00, 300.00 and 600.00 |

| Custom Product | Description  |  |
|----------------|--|--|
| Contact Molex  | Micro-Fit Discrete Wire Cable Assembly, Custom Lengths and Other Options |  |

| Series        | Description  | Circuit        | Lengths (mm)           |
|---------------|--|----------------|------------------------|
| <u>45132</u>  | Off-the-Shelf Micro-Fit Dual-Row TPA Discrete<br>Wire Cable Assemblies   | 4, 6, 8        |                        |
| <u>145132</u> | Off-the-Shelf Micro-Fit Single-Row TPA Discrete<br>Wire Cable Assemblies | 2 to 7         |                        |
| 214755        | Off-the-Shelf Micro-Fit Dual-Row non TPA Discrete                        | 2, 4, 6, 8, 10 | 150.00, 300.00, 600.00 |
| <u>214756</u> | Wire Cable Assemblies  |                |                        |
| <u>214757</u> |  |                |                        |
| <u>214758</u> |  |                |                        |

| Series        | Description  | Circuits             | Lengths (mm)           |
|---------------|--|----------------------|------------------------|
| <u>214750</u> |  |                      |                        |
| <u>214751</u> | OTS Micro-Fit 3.0 DR Discrete Wire Cable Assemblies Gold and Tin | 2, 3, 4, 5, 6, 8, 10 | 150.00, 300.00, 600.00 |
| <u>214752</u> | OTS MICTO-FIL S.O DE DISCIPLE WITE CADIE ASSEMBILES GOID AND THE |                      |                        |
| <u>214753</u> |  |                      |                        |

#### www.molex.com/link/otscableassemblies.html