

Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor


Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'GE255-L'

Your search criteria matched only one product, shown below

GE255-L



Part Number	GE255-L
RoHS Compliancy Status	Compliant
Part Description	Military Specification Nylon Grommet Edging in 12.75" strips.
Material	Nylon 6.6
Color	Natural
Military Specification	MS21266-5N
Height (In.)	.24
Height (mm)	6.1
Length (In.)	12.75
Length (mm)	323.9
Width (In.)	.39
Width (mm)	9.8
Flammability Rating	UL94 V-2
Outside Depth (In.)	.240
Outside Depth (mm)	6.1
Outside Width (In.)	.385
Outside Width (mm)	9.8
Panel Thickness Range (In.)	.192 – .255
Panel Thickness Range (mm)	4.9 – 6.5
Pricing Description	Grommet Edging, Slot Strip, Nylon, Natural
Temperature Range	-40°F to 149°F (-40°C to 65°C)
Min. Order UOM	PC
Min. Order Qty.	50
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.