

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200651787](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (M12) Single-Ended Cordset, 5 Poles, Female (90°) to Pigtail, 0.34mm² PUR/PVC Cable 10.0m (32.81') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|--------------------|--|
| Product Family | Industrial Cordsets |
| Series | 120065 |
| Connector End A | Micro-Change (M12) |
| Connector End B | Pigtail |
| IP Rating | IP67 |
| Material - Contact | Copper Alloy |
| Overview | Brad Micro-Change (M12) Connectors |
| Product Name | Micro-Change (M12) |
| Protocol | N/A |
| Region | Europe |
| Type | Single Ended |
| UPC | 78172553166 |

Physical

| | |
|-------------------------------|---------------------|
| Cable Diameter | 5.30mm (.209") |
| Cable Length | 10.0m (32.81') |
| Color - Cable Jacket | Black |
| Coupling Style | Threaded |
| Gender | Female-Pigtail |
| Keyway | Single |
| LED Indicator | No |
| Material - Cable Jacket | PUR/PVC |
| Material - Connector Body | PUR |
| Material - Coupling Nut | Nickel-plated Brass |
| Material - O-Ring | Fluoro-elastomer |
| Material - Plating Mating | Gold |
| Net Weight | 341.335/g |
| Orientation | 90° to Pigtail |
| Poles | 4 |
| Temperature Range - Operating | -20°C to +80°C |
| Wire Size AWG | N/A |
| Wire/Cable Type | EU Cable |

Electrical


| | |
|-------------------------------|------------|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 250V AC/DC |

Material Info

| | |
|--------------------|---------------|
| Engineering Number | 804001P03M100 |
|--------------------|---------------|

Reference - Drawing Numbers

| | |
|---------------|----------------|
| Sales Drawing | 1200658573-000 |
|---------------|----------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[120065 Series](#)