

Product finder

Search help

Search Pulse products by Keyword or Part number

Search

product groups connectors optical networking product sfpp-3130-l

[Back to results page](#)

SFPP-3130-L

Part number: SFPP-3130-L |  Active product [What is this?](#)



| | |
|--------------------------|----------------------|
| Application - LAN | |
| Connector Type | SFP CAGE & CONNECTOR |
| Speed | 10GBASE-T |
| Number of Ports | 2x2 |
| Package | PRESS FIT |

[Detailed info](#)

Documents

Data Sheets [Datasheet SFPP-3130-L.PDF](#)

Attributes

| | |
|------------------------------------|----------------------|
| Connector Type | SFP CAGE & CONNECTOR |
| Contact Mating Area Plating | GOLD 30 u" |
| FRE Logo | NO |
| Housing Material | NYL ON +33% GF |
| Keyed | NO |
| LED Option | LIGHT PIPES |
| Latch | NOT APPLICABLE |
| Number of Contacts | 20 |
| Number of Ports | 2x2 |
| Number of Positions | 20 |
| PCB | NO PCB |
| PCB Mount Angle | SIDE ENTRY |
| Package | PRESS FIT |
| Package Height (mm) | 25.3 |
| Package Length (mm) | 63.25 |
| Package Width (mm) | 29.06 |
| Panel Stop | NO |
| Pin Shape | STAMPED/SQUARE |
| RoHS Compliant | YES - RoHS-6 |
| Search | YES |

Product Finder or Keyword

StockCheck Distributor Inventory

Find what you need

[Search Center](#)
[User Center](#)

[Application Support](#)
[Competitor XRef Search](#)
[IC XRef Search](#)
[Product Finder](#)
[Data Sheets](#)
[Contact Us](#)
[Distributors](#)
[Representatives](#)
[Offices](#)
[Quote/ Sample](#)
[Product Catalog](#)
[Literature Request](#)