




**2 x 5mm Rectangular**  
*microLED*® *Optopipe*™  
**Optical Light Pipe, Single**



**515-1054**



**MicroLED SMT LEDs**  
**for use with 515-1054**

<u>PART NO.</u>	<u>PAGE #</u>
<b>Recommended</b>	
597-3xx1-2xx	1-21
597-77x1-2xx	1-23
<b>Alternatives</b>	
597-3xx1-5xx	1-30
597-77x1-5xx	1-31

LED alternatives may not produce optimum light output

Solder Pad/Holes layout shown is for single color LEDs listed under "Recommended" category

Contact factory for other layouts

**Features**

- Compatible with Dialight's 515-1051
- High transmissivity polycarbonate material
- UL94V-0 compliance
- ESD protection (circuit isolation from front panel)
- Wide viewing angle
- Secures to PCB by press-fit

**LED Data**

For absolute maximum ratings and other electrical and optical data on the recommended LEDs, refer to LED data sheets.

**Operating/Storage Temperature**

-30°C to +100°C

**Dialight Optopipe Light Pipe Description**

This Optopipe™ functions as a through-the-case indicator with the appearance of a single 2 x 5mm rectangular LED. It can utilize either a single or multi-color SMT LED, and can be used to form longer arrays with the 515-1051 light pipe. It is held to the PCB by 2 press-fit pins. The light pipe material is water clear transmissive polycarbonate rated UL94-V0, and has a 35% oxygen index.

Dialight can provide custom Optopipe™ solutions for your applications.