



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



TEAR TAB

FULL SCALE

B

B

TO APPLY LATCHING WIRE CLIP:
1. REMOVE PROTECTIVE LINER
2. PLACE IN DESIRED LOCATION
3. APPLY PRESSURE TO TOP OF LATCHING WIRE CLIP

NOTES:
*1) SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.

2) MOUNT IS DESIGNED TO SUPPORT 0.50 lbs (227g) MAX WEIGHT ON A CLEAN DRY SMOOTH SURFACE.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE, AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED, AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED, ARE BEYOND PANDUIT'S CONTROL.

ADHESIVE BACKING: PRESSURE SENSITIVE FOAM 0.04 (1.0) THICK WITH PROTECTIVE LINER TO EXTEND BEYOND EDGE FORMING A TEAR TAB.

DIMENSIONS IN BRACKETS ARE METRIC (mm)

TITLE									
LWC38-A, LATCHING WIRE CLIP									
CUSTOMER DRAWING									
ITEM REVISION NAME									
108015KH/00									
DATASET FILE NAME									
108015KH-DC/00 - G801608A-REV02									
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)									
.X : 0.05 (1.3) .XXX : 0.010 (0.25) .XX : 0.02 (0.5) ANGLES : 5°									
THIRD ANGLE PROJECTION									
DRAWN BY DATE									
JRL 11-11-93									
CHK SCALE									
2X									
MATERIAL:									
NYLON 6/6									
DRAWING NUMBER:									
G801608A									
SHT 1 OF 1									
SIZE									
A									

A

A