

FEATURES

- 316 Stainless Steel
- 150 lbs fitting
- BSPT tapered screw end
- Various sizes available
- S/40 pipe Hexagon plug

RS PRO Stainless Steel Hexagon Plug 1/2in R(T) Male 0.89in

RS Stock No.: 499-3467



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Stainless Steel Threaded Fittings



Product Description

Brought to you by RS Pro, a series of stainless steel threaded fittings, suitable for applications requiring a secure and reliable pipe connection. Heavily used within the plumbing industry, water and gas will flow through in a tightly sealed construction. These hexagon plug fittings are made from a durable 316 stainless steel to ensure a simple and secure connection for pipe and hose work. All models are highly reliable and excellent quality.

General Specifications

Connection 1	1/2 in R Male
Shape	Hexagon
Fitting Type	Plug
Thread Size 1	1/2in
Connection Gender 1	Male
Thread Standard 1	R (taper)
Material	316 Stainless Steel
Application	All throughout the home (bathroom, kitchen etc.)Any building with running water, heating or gas; Sewage and underground networks; Ships and boats; Car engines

Mechanical Specifications

Length	0.89in	

Stainless Steel Threaded Fittings





Standard Pattern

SIZE	1/8"		1/4"		3/8"		1/2"		3/4"		1"		1-1/4"		1-1/2"		2"		2-1/2"		3"		4"	
	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in										
Н	10.5	0.41	12	0.47	13.5	0.53	16	0.63	16.5	0.65	19	0.75	21	0.83	21	0.83	22.8	0.,9	29	1.14	29.3	1.15	30.8	1.21
L	16.2	0.64	18	0.71	19.5	0.77	22.6	0.89	23.3	0.92	26.8	1.06	30.5	1.2	30.8	1.21	34	1.34	40.5	1.59	41.7	1.64	44.8	1.76
W	13.2	0.52	16.6	0.65	19.3	0.76	25.2	0.99	29.7	1.17	36.5	1.44	45.3	1.78	51.4	2.02	62.5	2.46	79.5	3.13	92	3.62	117.5	4.63

Tolerance: ±0.5mm(1/8"~2")

±0.8mm(2-1/2"~4")