


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO. *	'A' MAX.	'B' MIN.	STACKING HEIGHT 'H' WHEN USED WITH INTERMEDIATE STRAP				WEIGHT lbs / 100 (g) / pcs.
			PLT1.5I	PLT2I	PLT3I	PLT4I	
FCPI1	1.29 (32.8)	1.04 (26.4)	0.8 (20.3)	2.0 (50.8)	3.7 (94)	5.2 (132.1)	.18 (81.7)
FCPI2	2.31 (58.7)	2.04 (51.8)	-----	1.0 (25.4)	2.7 (68.6)	4.2 (106.7)	.34 (154.4)
FCPI3	3.32 (84.3)	3.04 (77.2)	-----	-----	1.7 (43.2)	3.2 (81.3)	.52 (236.1)



TYPICAL INSTALLATION OPTIONS

DIMENSIONS IN BRACKETS ARE METRIC (mm)

600239KV_PB_FCP1_00

PANDUIT

TINLEY PARK, ILLINOIS

FLAT CABLE MOUNT PLATE
(FCPI-)

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (1.0XX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ±5°

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JAD MAT'L

SCALE NONE

DATE 9/23/03

NYLON 6/6

DRAWING NO.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
R	9/23/03	JAD		INITIAL RELEASE, REPLACES SS-05546	600239KV	R		

COLOR: BLACK

GB0239KV

SIZE

A

- NOTES
- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
 - FCPI2 CAN BE USED WITH BASE FCBI2, SEE PANDUIT DRAWING GB0239HY