





PRODUCT NO.
SEE TABLE



mat'l. code	surface	tolerance	projection	product family
ISD1302	ISD1302	ISD1302	ISD1302	MOD JACK
trlec naddr	tolerances unless otherwisespecified			
R S00022	date	angle	mm	
S N05-0002	01/26/00	0°	scale 2.0	
T N06-0130	01/07/05	0°		
U N08-0097	LONG 5/15/06	0° ±2'		
V ELX-N-010696	SI MM 5/10/08	0°		
	engr TONY CHIEN	JANET	01/26/00	
	chr TONY CHIEN	TONY CHIEN	01/26/00	
	appd JENN TSAO	JENN TSAO	01/26/00	
sheet revision	v			
index sheet	1	2		

awg no	sheet of 2	size
6 POS HORIZONTAL		A4
P.C.B. MOD JACK ASSY		
68898		
type	Product	Customer Drawing




A

B

B


PRODUCT NO. (NOTE 1)	POSITIONS LOADED	CONTACT PLATING	HOUSING COLOR	REMARKS
68898-001/-001LF	ALL	5u" Au + high performance lubricant @ TM	BLACK	YES
68898-001R/-001RLF	ALL	5u" Au + high performance lubricant @ TM	RED	YES
68898-001G/-001GLF	ALL	5u" Au + high performance lubricant @ TM	GREEN	YES
-002/-002LF	2,3,4,5	5u" Au + high performance lubricant @ TM	BLACK	YES
-003/-003LF	3,4	5u" Au + high performance lubricant	BLACK	YES
-004/-004LF	2,3,4,5	5u" Au + high performance lubricant	BLACK	YES
-005/-005LF	ALL	5u" Au + high performance lubricant	BLACK	YES
-006/-006LF	3,4	5u" Au + high performance lubricant @ TM	BLACK	YES
007	2,3,4,5	GXT @ TM	GRAY	YES
-008/-008LF	ALL	5u" Au + high performance lubricant	BLACK	NO
-009/-009LF	2,3,4,5	1,27um /50u" GXT	BLACK	YES
-010/-010LF	ALL	1,27um /50u" GXT	BLACK	YES
-011/-011LF	2,3,4,5	2u" GXT	BLACK	YES
-012/-012LF	2,3,4,5	6u" GXT	BLACK	YES
-013/-013LF	ALL	5u" Au + high performance lubricant @ TM	BLACK	YES
-014/-014LF	3,4	6u" GXT	BLACK	YES
-015/-015LF	3,4	5u" Au + high performance lubricant @ TM	BLACK	NO
-016/-016LF	2,3,4,5	5u" Au + high performance lubricant @ TM	BLACK	NO
-017LF	ALL	5u" Au + high performance lubricant @ TM	BLACK	YES



VIEW A-A

NOTES :

- 1 WHEN PRODUCT CALLS FOR PACKAGING IN TRAY ORDER THE PRODUCT WITH PART NUMBER 68898-XXXT OR -XXXTLF FOR PACKAGING IDENTIFICATION.
- 2 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 3 IF LF P/N PACKAGING MEETS GS-14-920 SPECIFICATION.
- 4 THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.60mm MINIMUM THICK CIRCUIT BOARD.
- 5 FOR 68898-013/013LF THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- 6 EQUIVALENT THICKNESS Au AND GXT PLATING HAVE SAME FUNCTION AND THEY ARE ALTERNATIVE BY THE CUSTOMER .



mat'l. code	surface	tolerance	projection	product family
ISDI302	ISDI302	ISDI302	ISDI302	MOD JACK
tracen naddr	date	tolerances unless otherwisespecified	title	
R S00022	01/26/00	0.X±0.3		
S N05-0002	01/07/05	0.XX±0.15		
T N06-0130	05/15/06	0.XXX±0.05		
U N08-0097	05/10/08			
V ELX-N-010696	03/14/12			
	JANET	01/26/00		
	TONY CHIEN	01/26/00		
	CHR TONY CHIEN	01/26/00		
	APPD JENN TSAO	01/26/00		
sheet index	revision			
	Sheet			

6 POS HORIZONTAL
P.C.B. MOD JACK ASSY
awg no sheet 2 of 2 size
68898 A4
type Product Customer Drawing

