



Industrial & Electrical Components

Relay Socket


Part No.

PYF08A
PYF11A
PYF14A

PYF08A




OUTLINE DIMENSIONS



SPECIFICATION

Rated Load	Current	5A
	Voltage	300V
Dielectric Strength		2500V
Ambient Temperature		-40~+75°C
Socket Material		Flame retardance PA66+GF(V1/V0)
Contacts Spring Material		QSn6.5-0.1
Clamp Spring Material		Plastic
Module		No


DIAGRAM



PYF11A




OUTLINE DIMENSIONS



SPECIFICATION

Rated Load	Current	5A
	Voltage	300V
Dielectric Strength		2500V
Ambient Temperature		-40~+75°C
Socket Material		Flame retardance PA66+GF(V1/V0)
Contacts Spring Material		QSn6.5-0.1
Clamp Spring Material		Plastic
Module		No


DIAGRAM



PYF14A



OUTLINE DIMENSIONS



SPECIFICATION

Rated Load	Current	5A
	Voltage	300V
Dielectric Strength		2500V
Ambient Temperature		-40~+75°C
Socket Material		Flame retardance PA66+GF(V1/V0)
Contacts Spring Material		QSn6.5-0.1
Clamp Spring Material		Plastic
Module		No

DIAGRAM

