

Industrial & Electrical Components

Relay Socket


Part No.

PYF08A-E2
PYF14A-E2

PYF08A-E2




OUTLINE DIMENSIONS



SPECIFICATION

Rated Load	Current	7A
	Voltage	300V
Dielectric Strength		2500V
Ambient Temperature		-40~+75°C
Socket Material		Flame retardance PA46-S250F6(V0)
Contacts Spring Material		QSn6.5-0.1
Clamp Spring Material		Steel
Module		Optional


DIAGRAM



PYF14A-E2



OUTLINE DIMENSIONS



SPECIFICATION

Rated Load	Current	7A
	Voltage	300V
Dielectric Strength		2500V
Ambient Temperature		-40~+75°C
Socket Material		Flame retardance PA46-S250F6(V0)
Contacts Spring Material		QSn6.5-0.1
Clamp Spring Material		Steel
Module		Optional

DIAGRAM

