



DIGITAL CONTROL DC POWER SUPPLY



**QJ3005T**

**FEATURES**

- 1.10mV/1mA setting resolution
- 2.Low noise and ripple
- 3.Over-current protection
- 4.Setting lock prevents circuit damage
- 5.Large LED display
- 6.Linear design
- 7.Robust construction-perfect for education,industrial and professional users

**Specifications**

Models	QJ3005T
Channel	Single channel
Output voltage	0~30V
Ripple & noise	≤ 1.0mV(rms)
Output current	0~5A
Ripple Current	3mA(rms)
Short Circuit & Overload Protection	
AC input	AC220V±10%
Frequency	50/60Hz±2HZ
Operating Temperature	0~+40℃ ,<90% RelativeHumidity
Safety Standard	CE

- All values are based on the standard ambient Temperature 25℃ and Pressure 0.1Mpa
- SPECIFICATIONS ARE SUBJECTTO CHANGE WITHOUT PRIOR NOTICE