


		1	
Part Number:		DRAWN	12/21/2010
CMOZO	0508-2	CJ	12/31/2018
SW8/U		CHECKED	1/7/2010
		C.H.	1/7/2019
Description:	of Speaker	APPROVED	1/7/2010
waterprod		C.E.	1/7/2019

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com

Top View



-30 ~ +180

3.0


2.0

Gasket Temperature Range


Gasket Thickness

Gasket Width

Side View



Bottom View



2) All tolerances are ± 0.5 mm unless otherwise noted
3) All parts meet RoHS

4) Subject to change or redrawn without notice

Items	Specifications	Conditions					
Sound Pressure Level	103	dB (1W@10cm), Avg.					
Resonant Frequency	500	Hz					
Frequency Range	500 ~ 7,000	Hz					
Nominal Power	10	W					
Max. Power	16	W					
Impedance	8	Ω					
Cone Material	PET		REVISION HISTORY				
Mount Type	Frame Mount		REV	DESCRIPTION	DATE	APPROVED	
IP Rating	IP67			Released from Engineering	1/7/2019	C.E.	
Storage Temperature	-30 ~ +70	°C	1	Standardized call-out text	8/7/2019	C.E.	
Operating Temperature	-20 ~ +60	°C	2	Updated SPL distance	8/12/2019	C.E.	
Weight	240	g	3	Updated drawing, SPL and added gasket info	8/28/2019	C.E.	
Gasket Material	NBR5		NOTES				
Gasket Durometer	70 shore A		1) All dimensions are in mm unless otherwise noted				

°C

mm

mm