

Tripp Lite

1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

4-Port USB Charging Station, 5V 6A/30W USB Charger Output

MODEL NUMBER: U280-004











Charges up to 4 electronic devices at the same time via USB connection. Ideal for quick-charging tablets, cell phones, laptops and other mobile devices.

Description

Whether you're at home or in the office, Tripp Lite's U280-004 4-Port USB Charging Station provides enough ports and power to keep your devices at 100% capacity. No more peering behind furniture to find an available outlet or unplugging one device to charge another. You can charge up to four tablets, cell phones, laptops and other devices at the same time. The U280-004 doesn't require a computer, so you can take it anywhere AC power is available.

The U280-004 simultaneously provides up to 5V, 1.5A of power per port at maximum capacity. Each individual port supports USB Battery Charging (BC) specification v1.2 and is capable of delivering up to 5V, 2.4A, which is enough for charging even battery-intensive devices like the Apple® iPad®.

To charge your USB devices, simply connect the four-foot power cord's NEMA 1-15P plug to an AC power outlet, and connect your devices to the available USB ports. The unit protects against overheating, overcurrent and overcharging—in fact, it stops charging as soon as your devices' batteries are at full capacity. A front LED indicates the unit is turned on and receiving AC power.

Features

Charges Up to 4 Devices at the Same Timeldeal for charging tablets, cell phones, laptops and other devices at home or workConnect devices to unit's USB ports for proficient chargingFunctions anywhere AC power is available—no computer required

Provides Plenty of Juice for ChargingEach individual port capable of delivering up to 5V, 2.4A, enough for charging battery-intensive devices like the Apple iPadSimultaneously provides up to 5V, 1.5A of power per port at maximum capacityAll four ports support USB Battery Charging (BC) specification v1.2Protects against overheating, overcurrent and overcharging

Easy to Use4 ft. power cord with NEMA 1-15P plug connects to AC outletFront LED indicates when unit is turned on and receiving AC power

Specifications

OVERVIEW

Highlights

- 5V, 2.4A per port for charging battery-intensive devices
- 5V, 1.5A per port simultaneously when at maximum capacity
- All four ports support USB Battery Charging (BC) specification v1.2
- Internal dual-voltage power supply with NEMA 1-15P plug
- Protects against overheating, overcurrent and overcharging
- No computer required

Package Includes

- U280-004 4-Port USB Charging Station
- C7 to NEMA 1-15P power cord,
 4 ft.
- Quick Start Guide





UPC Code	037332192073	
Product Type	Plug in Charger	
Charging Form Factor	Charging Hub	
Device Compatibility	Phone; Tablet; Amazon Kindle	
Technology	USB	
INPUT		
Nominal Input Voltage(s) Supported	120V AC; 230V AC	
Plug Type	C7 to NEMA 1-15P	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240	
Input Frequency	50/60Hz	
Input Plug Type	NEMA 1-15P	
Input Current	120V (0.8A) / 230V (0.4A)	
OUTPUT		
Overload Protection	Yes	
USER INTERFACE, ALERTS & CON	ITROLS	
LED Indicators	Blue (Power)	
CHARGING		
Number of Charging Ports	4	
Total Charging Amps	6A	
Total Charging Watts	30	
Charging Method	USB	
Charging Port Type	(4) USB A (FEMALE)	
Charging Ports Details	USB-A: 5V 2.4A (12W)USB-A: 5V 1.5A (7.5W) when all ports are in use	
Charging Ports / Amps	(4) 2.4A	
Charging Method Detail	5V - 1.5A (7W)	
PHYSICAL		
Color	White	
Shipping Dimensions (hwd / cm)	5.08 x 13.46 x 18.54	
Shipping Dimensions (hwd / in.)	2.00 x 5.30 x 7.30	
Shipping Weight (kg)	0.45	
Shipping Weight (lbs.)	1.00	
Unit Dimensions (hwd / cm)	3.1 x 10.6 x 10.1	





Unit Dimensions (hwd / in.)	1.2 x 4.2 x 4.0	
Unit Packaging Type	Box	
Unit Weight (kg)	0.21	
Unit Weight (lbs.)	0.46	
ENVIRONMENTAL		
Operating Temperature Range	41°F to 95°F / 5°C to 35°C	
Storage Temperature Range	-4°F to 122°F / -20°C to 50°C	
Relative Humidity	20% to 80% RH, Non-Condensing	
Power Consumption (Watts)	38	
Power Consumption Detail	38W (Operating) 0.26W (Standby)	
CONNECTIONS		
Ports	4	
Side A - Connector 1	NEMA 1-15P (NON-POLARIZED)	
Side B - Connector 1	(4) USB A (FEMALE)	
SPECIAL FEATURES		
Overcurrent Protection	Yes	
Overvoltage Protection	Yes	
GaN Technology	No	
STANDARDS & COMPLIANCE		
Certifications	Tested to FCC, RoHS, REACH	
Approvals	UL Listed	
WARRANTY		
Product Warranty Period (Worldwide)	2-year limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies