

SPECIFICATIONS				
VALUES	UNITS	T F		
2	W	7		
4	W	1		
4 ± 15%	OHM			
86 ± 3	dBA	1		
5%	-			
370 ± 20%	Hz			
Fo ~ 20,000	Hz			
ABS	-			
TREATED PAPER	-			
Nd-Fe-B	-			
-40 ~ +80	°C			
16.5	grams			
	VALUES  2  4  4 ± 15%  86 ± 3  5%  370 ± 20%  Fo ~ 20,000  ABS  TREATED PAPER  Nd-Fe-B  -40 ~ +80	VALUES       UNITS         2       W         4       W         4 ± 15%       OHM         86 ± 3       dBA         5%       -         370 ± 20%       Hz         Fo ~ 20,000       Hz         ABS       -         TREATED PAPER       -         Nd-Fe-B       -         -40 ~ +80       °C		

THIS DOCUMENT CONTAINS DATA PROPRIETARY
TO PROJECTS UNLIMITED, INC. ANY USE OR
REPRODUCTION, IN ANY FORM, WITHOUT PRIOR
WRITTEN PERMISSION OF PROJECTS UNLIMITED,
INC. IS PROHIBITED.

©2003, Projects Unlimited Inc.

Υ	REVISION HISTORY				
R	LTR	DESCRIPTION	DATE	APPROVED	
Р,	-	RELEASED FROM ENGINEERING	12/7/2005		
	Α	ADDED MOUNTING HOLE DIMENSION	12/18/2007	R.W.	
	В	REVISED MAX. INPUT POWER	7/18/2008	B.R.	
	С	REVISED OPERATING TEMPERATURE	10/14/2008	C.W.	
	D	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	11/8/2008	B.R.	
	Е	ADDED NOTE 5	8/11/2011	B.R.	
	F	FIX POLARITY, UPDATE ROHS STATUS AND NOTES	3/5/2015	M.L.	
	G	ADJUST RESONANT FREQUENCY RANGE TO READ FO	5/3/2017	M.L.	







## NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
- 3. THIS PART IS RoHS 2011/65/EU COMPLIANT.
- 4. CONE HAS BEEN TREATED FOR WATER RESISTANCE.
- 5. BASE SPEAKER PART# AS04004PO-R

UNLESS OTHERWISE SPECIFIED:	CIZE
DIMENSIONS ARE IN MILLIMETERS,	SIZE
TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.	<b>A</b> 3
AS04004PO	-WR-R.idw

$\sim$				1.00.4	00.40	0 14/0	
	J.A.F.	12/6/2005	B.R.	12/7/2005	E.P.	12/7/2005	11/8/2008
	Designed by	Date	Checked by	Date	Approved by	Date	Drawn Date



AS04004PO-WR-R

1/1

Speaker