

Products

- Products Overview
- Product Search**
- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - DXF-Type G 2x5 W ..
 - PDFType G 2x5 W ..
 - DWG-Type G 2x5 W..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor


Home > Products Overview > Product Search >

Current refinements (click  to remove) Search Tips

Pricing Description > Slotted Duct, PVC,2"X5"X6',ADH,LGRY

Your search criteria matched only one product, shown below

G2X5LG6-A




Choose from 36 sizes of Panduit® Type G Wiring Duct from 0.5" x 0.5" up to 6.0" x 4.0" in popular colors. Used for general purpose control panel wiring and to route and protect wiring in communication closets. The non-slip cover conceals all wiring and is easy to install. The duct and cover form a flush sidewall providing increased capacity and improved aesthetics.

Specifications

- **Base and covers sold separately**
- Made of lead-free PVC
- UL Recognized continuous use temperature: 122 °F (50°C)
- UL94 Flammability Rating of V-0
- Conforms with NFPA 79 -2002 section 14.3.1 requirement for flame retardant material
- Provided with mounting holes

Features and Benefits

- Wide finger/slot design provides greater sidewall rigidity and can be used with a wide range of wire bundle sizes
 - Panduit® exclusive rounded edges protects hands and wiring/cabling from abrasion
 - Non-slip cover stays in place during shipment, vibration and when in vertical orientation, eliminating rework
 - Flush cover design holds 10 -12% more wires than traditional duct designs
 - Double scoreline allows quick modification for larger cabling bundles saving installation time leading to a lower installed cost
 - Specially formulated lead -free material eliminates health concerns associated with PVC that contains lead
 - Restricted slot design retains wire in slot for fast, easy wire installation or removal
- Base and cover sold separately.

Part Number	G2X5LG6-A
RoHS Compliancy Status	Compliant
Part Description	Wide finger, slotted wiring duct. Base and covers sold separately. Base and covers sold separately.
Product Type	Type G Wide Slot Wiring Duct
Material	Lead- Free PVC
Color	Light Gray
CSA Certified	Yes
UL Recognized (File No. E147128)	Yes
Height (In.)	5.10
Height (mm)	129.5
Length (ft.)	6
Length (mm)	1828.8
Width (In.)	2.25
Width (mm)	57.2
Adhesive Mounting Tape	Yes
CE Compliant	Yes
Duct Size W x H (In.)	2.25 x 5.10
Duct Size W x H (mm)	57.2 x 129.5
Mounting Method	Standard Mounting Holes with Adhesive
Pricing Description	Slotted Duct, PVC,2"X5"X6',ADH,LGRY
Slot Width (In.)	0.38
Slot Width (mm)	9.7
Cover Part Number	C2LG6
Min. Order UOM	FT
Min. Order Qty.	6
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.