



Fuse-link, LV, 125 A, AC 690 V, NH00, gL/gG, IEC, dual indicator, live gripping lugs

Catalog No. 125NHG00B-690

EL-Nummer (Norway) 0001664111

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	125
Rated voltage			AC 690 V
Construction size			NH00
Utilization category			gL/gG
Status indicator			dual (combination) indicator system
Description			live gripping lugs
Breaking Capacity		kA	120
Standard/Approval			IEC
Shape			square body with knife blade contacts
Standards/Regulations			IEC 60269-2 fuse system A DIN 43620 VDE 0636-2

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			NH00
Rated current		A	125
Rated voltage		V	690
Voltage type			AC
Rated switching capacity		kA	120
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			Combination fuse status indicator
Insulated metal gripping lugs (IMGL)			No

Additional product information (links)

Product datasheet (PDF)	http://www.cooperindustries.com/content/dam/public/bussmann/iec-electrical/resources/data-sheets/bus-iec-ds-720109-nh690vfuselinks.pdf
-------------------------	---