

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0510650700](#)
Status: **Active**
Overview:
Description: 2.00mm Pitch, Micro-Latch Receptacle Crimp Housing, Single Row, 7 Circuits, Natural

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	51065
Application	Signal, Wire-to-Board
Overview	microlatch
Product Name	Micro-Latch
UPC	800753574281

Physical

Circuits (maximum)	7
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	182.600/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-51065-001-001
Product Specification	510650000-PS-000, 510650001-PS-000, 510651000-PS-000, 510651001-PS-000
Sales Drawing	510650000-SD-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[51065](#) Series

Mates With

[53253](#) PCB Header, [53254](#) PCB Header

Use With

[50212](#) Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION