

A.301MTJ1 | A.MTJ1 - MICRO-TECH® TORQUE SCREWDRIVER SETS




Norm :

NF EN ISO 6789, ISO 6789, DIN EN ISO 6789

Description :

- Lightweight and compact screwdriver for low torque load.
- Right-hand torquing.
- Female hex output for use with bits series 0 - 4 mm (1/4" output with ECR.O drive optional).
- Bits series 0 drive 4 mm.
- Adjustment key 4 mm.
- Supplied in case with calibration certificate.

Informations :

	A.301MTJ1
Capacity [cN.m]	15 - 75
Bits	Slotted head: 4 - 4,5 - 5,5 ; PH: 1,5 - 2,5 - 3 mm ; PZ: 0 - 1 mm
Screwdriver	A.301MT
[g]	370