

Search within category **GO**

BUY NOW

DESIGN / INSTALL

PRT2S-M6

Pan-Ty® releasable tie, standard cross section, 7.4 (188mm) length, nylon 6.6, blue.

Specs **Packaging Details** **Documents** [★ Add to Favorites](#) [Add to BOM](#)

Material	Nylon 6.6
Overall Length (In.)	7.4
Overall Length (mm)	188
Color	Blue
Overall Width (In.)	0.19
Overall Width (mm)	4.8
Minimum Loop Tensile Strength (N)	222
Minimum Loop Tensile Strength (lb)	50
Maximum Installation Temperature (°F)	32
Application	General
Cross Section	Standard
Length (In.)	7.40
Length (mm)	188.0
Locking Style	Releasable
Plenum-Rated	Yes, AH-2
UV Resistant	No
Tool	Hand install only
Thickness In (mm)	0.05 (1.3)
CE Compliant	Yes
CSA Certified	Yes
UL 62275 Compliant (Type 2S, 21S)	Yes
UL Listed (File #E56854)	Yes
UL Recognized (File #E56854)	Yes
Continuous Use Temperature Range	-76°F (-60°C) - 185°F (85°C)
Operating Temperature	-76°F (-60°C) - 185°F (85°C)
Part Features	Release tab permits easy release and re-use where changes are anticipated.
RoHS Compliancy Status	Compliant
Min. Order Qty.	1,000

