

FEATURES

- Conforms to the latest requirements of British and European standards.
- Cable gland design provides external clamping
- Lockable protection window on all variants to enhance safety
- Screw terminals accept conductors up to 2.5mm² for 16A, 6mm² for 32A, 16mm² for 63A and 50mm² for 125A types
- IP67 and IP66 rated
- Red, blue and yellow colours offered in this range of power connectors
- Voltage ratings of 110V, 230V and 415V offered in this range
- Halogen free

RS PRO IP66, IP67 Blue Cable Mount 2P+E Industrial Power Socket, Rated At 32.0A, 230.0V

RS Stock No.: 724-9221



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted brand RS PRO, comes a range of high-quality cable mounted free socket power connectors. Manufactured to industry standards these connectors are easy to assemble and are a fantastic industrial plug solution for powering tools and machinery at a range of different voltage requirements.

General Specifications

Pole Format	2P+E
Hour Position	6h
Gender	Female
Body Orientation	Straight
Material	Engineering Plastic
Colour	Blue
Applications	Providing power for machinery on construction sites, Woodworking machines, Maintenance workshops in the light industry

Electrical Specifications

Current Rating	32A
Voltage Rating	200-250V
Working Frequency	50Hz, 60Hz
Plug/Socket	Socket
Termination Method	Screw
Cable CSA	6.0mm ²

Operation Environment Specifications

Maximum Operating Temperature	40°C
Minimum Operating Temperature	-25°C

Mechanical Specifications

Mounting Type	Cable Mount
---------------	-------------

Protection Category

IP Rating	IP66, IP67
-----------	------------

Approvals

Compliance/Certifications	EN 60309-1, EN 60309-2
---------------------------	------------------------

