



n = poles No.
Find more technical information on drawings DS 15211100301

Part Number	poles no.	A	B	C	D	E	G
15 23 006 x601 xxx	06	2,54	6,96	8,89	5,56	4,56	1,19
15 23 008 x601 xxx	08	3,81	8,23	10,16	6,83	5,83	1,19
15 23 010 x601 xxx	10	5,08	9,50	11,43	8,10	7,10	2,46
15 23 012 x601 xxx	12	6,35	10,77	12,70	9,37	8,37	2,46
15 23 014 x601 xxx	14	7,62	12,04	13,97	10,64	9,64	3,73
15 23 016 x601 xxx	16	8,89	13,31	15,24	11,91	10,91	3,73
15 23 018 x601 xxx	18	10,16	14,58	16,51	13,18	12,18	5,00
15 23 020 x601 xxx	20	11,43	15,85	17,78	14,45	13,45	5,00
15 23 022 x601 xxx	22	12,70	17,12	19,05	15,72	14,72	6,27
15 23 024 x601 xxx	24	13,97	18,39	20,32	16,99	15,99	6,27
15 23 026 x601 xxx	26	15,24	19,66	21,59	18,26	17,26	7,54
15 23 028 x601 xxx	28	16,51	20,93	22,86	19,53	18,53	7,54
15 23 030 x601 xxx	30	17,78	22,20	24,13	20,80	19,80	8,81
15 23 032 x601 xxx	32	19,05	23,47	25,40	22,07	21,07	8,81
15 23 034 x601 xxx	34	20,32	24,74	26,67	23,34	22,34	10,08
15 23 036 x601 xxx	36	21,59	26,01	27,94	24,61	23,61	10,08
15 23 038 x601 xxx	38	22,86	27,28	29,21	25,88	24,88	11,35
15 23 040 x601 xxx	40	24,13	28,55	30,48	27,15	26,15	11,35
15 23 040 x601 xxx	42	25,40	29,82	31,75	28,42	27,42	12,62
15 23 040 x601 xxx	44	26,67	31,09	33,02	29,69	28,69	12,62
15 23 040 x601 xxx	46	27,94	32,36	34,29	30,96	29,96	13,89
15 23 040 x601 xxx	48	29,21	33,63	35,56	32,23	31,23	13,89
15 23 050 x601 xxx	50	30,48	34,29	36,83	33,50	32,50	15,16
15 23 050 x601 xxx	52	31,75	36,17	38,10	34,77	33,77	15,16
15 23 050 x601 xxx	54	33,02	37,44	39,37	36,04	35,04	16,43
15 23 050 x601 xxx	56	34,29	38,71	40,46	37,31	36,31	16,43
15 23 050 x601 xxx	58	35,56	39,98	41,91	38,58	37,58	17,70
15 23 060 x601 xxx	60	36,83	41,25	43,18	39,85	38,85	17,70
15 23 060 x601 xxx	62	38,10	42,52	44,45	41,12	40,12	18,97
15 23 060 x601 xxx	64	39,37	43,79	45,72	42,39	41,39	18,97
15 23 060 x601 xxx	66	40,64	45,06	46,99	43,66	42,66	20,24
15 23 068 x601 xxx	68	41,91	46,33	48,26	44,93	43,93	20,24
15 23 070 x601 xxx	70	43,18	47,06	49,53	46,20	45,20	21,51
15 23 070 x601 xxx	72	44,45	48,87	50,80	47,47	46,47	21,51
15 23 070 x601 xxx	74	45,72	50,14	52,07	48,74	47,74	22,78
15 23 070 x601 xxx	76	46,99	51,41	53,34	50,01	49,01	22,78
15 23 070 x601 xxx	78	48,26	52,68	54,61	51,28	50,28	24,05
15 23 080 x601 xxx	80	49,53	53,95	55,88	52,55	51,55	24,05

Packaging	
tape & reel with 170pcs per reel	000
samples	333

Performance level	
PL1: >500 mating cycles	2
PLS4 : min 0,06µm Au over 0,7+0,2µm PdNi	5

All Dimensions in mm Original Size DIN A3		Scale 5:1	Free size tol.		Ref.
All rights reserved		Created by ZHUANGJ	Inspected by LUOK	Standardisation HOFFMANN	Date 2019-03-25
Department EL PD		Title har-flex Stk 13,65mm str. fem conn assembly			State Final Release
HARTING Electronics GmbH D-32339 Espelkamp		Type TB	Number 1523XXXX601XXX		Doc-Key / ECM-Nr. 100222441/UGD/004/C 500000149313
				Rev. C	Page 1/1