



<b>Order Code</b>	<b>TCK-102</b>
<b>Inductance</b>	3.3 $\mu$ H $\pm$ 20% (at 100 kHz / 250 mV)
<b>Impedance (DCR)</b>	18 m $\Omega$ max.
<b>Rated Current</b>	10 A max.
<b>Operating Temperature</b>	-40°C to +125°C



### Impedance Curve



### Outline Dimensions



#### Dimensions [mm]

Dimension	Value
A	6.5 $\pm$ 0.3
B	6.5 $\pm$ 0.3
C	4.2 max.
D	7.6 max.
E	1.5 $\pm$ 0.3
F	1.2 $\pm$ 0.3
G	3.0
H	8.5
I	2.5

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TRACO Power:](#)

[TCK-102](#)