


SERIES	PINS PER ROW	WIRE GAUGE	K	ASSEMBLED LENGTH	END OPTION	LATCH OPTION
PMSSD = Double Row PVC Cable	-02, -03	-16	-K = Keyed Polarization	-"XX.XX" = Wire length in inches (88.90 mm) 03.50" min.	-S = Single End	-LUS = Plastic Latch up, straight
PMSSDT = Double Row Blue *Teflon® Cable (24 AWG only)	-04, -05	-18			-D = Double End (Latch Required)	-LDS = Plastic Latch down, straight
PMSSS = Single Row PVC Cable	-08, -10	-206 (20 AWG/600 volts)				-LUX* = Plastic Latch up, crossed
PMSSST = Single Row Blue *Teflon® Cable (24 AWG only)	-15* (Standard sizes) *Only available for double row	-22				-LDX* = Plastic Latch down, crossed
		-24				*(PMSSD/PMSSDT only)

PMSSD, PMSSDT, PMSSS, PMSSST
Board Mates:
IPBT


*DuPont™ Teflon® is a registered trademark of the E.I. du Pont de Nemours and Company or its affiliates.

Notes:
Teflon® cable is intended for crimp only. Contact Samtec for solderable cable applications.


For wiring option information refer to drawing on web.



PMSS/PMSSST



PMSSD/PMSSDT





PMSSD/IPBT	
WIRE GAUGE	CURRENT RATING (PER PIN)
16 AWG	10.3 A
18 AWG	8.8 A
22 AWG	5.7 A
24 AWG	5.2 A

2 PIN POWERED


View complete specifications at: samtec.com?PMSSD, samtec.com?PMSSDT, samtec.com?PMSSS & samtec.com?PMSSST

IPBD	POSITIONS PER ROW	ROW OPTION	K	SERIES	WIRE GAUGE	01	T	SP
	-02, -03, -04, -05, -08, -10, -15 (Standard sizes)	-S = Single Row -D = Double Row	-K = Keyed Polarization	CC69L = Contact, Loose CC69R = Contact, Full Reel (4,000 Parts per Reel)	-2024 = 20 to 24 AWG -1620 = 16 to 20 AWG		-T = Tin	







-D



-S





TOOLING

Hand Tool: CAT-HT-169-1620-13 (16-20 AWG)
Hand Tool: CAT-HT-169-2024-13 (20-24 AWG)

Mini Applicator: CAT-MC-169-1620-XX-02 (16-20 AWG)
Mini Applicator: CAT-MC-169-2024-XX-01 (20-24 AWG)
Extraction Tool: CAT-EX-169-01

Note:
Some lengths, styles and options are non-standard, non-returnable.

View complete specifications at: samtec.com?IPBD, samtec.com?CC69L & samtec.com?CC69R

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[IPBD-05-D-K](#) [IPBD-03-S-K-M](#) [IPBD-10-S-K-M](#) [IPBD-14-D-K-M](#) [IPBD-15-D-K-M](#) [IPBD-05-S-K-M](#) [IPBD-02-S-K-M](#)
[IPBD-04-S-K-M](#) [IPBD-02-D-K-M](#) [IPBD-04-D-K-M](#) [IPBD-05-D-K-M](#) [IPBD-08-D-K-M](#) [IPBD-08-S-K-M](#) [IPBD-10-D-K-M](#)
[IPBD-03-D-K-M](#) [IPBD-13-D-K-M](#) [IPBD-02-D](#) [IPBD-05-S](#) [IPBD-03-D](#) [IPBD-02-S](#) [IPBD-03-S](#) [IPBD-10-D](#) [IPBD-05-D](#)
[IPBD-04-D](#) [IPBD-06-D](#) [IPBD-07-D](#) [IPBD-08-D](#) [IPBD-09-D](#) [IPBD-11-D](#) [IPBD-13-D-K](#) [IPBD-14-D-K](#) [IPBD-15-D-K](#)
[IPBD-08-S-K](#) [IPBD-09-S-K](#) [IPBD-10-D-K](#) [IPBD-10-S-K](#) [IPBD-11-D-K](#) [IPBD-12-D-K](#) [IPBD-06-D-K](#) [IPBD-06-D-K-M](#)
[IPBD-06-S-K](#) [IPBD-07-D-K](#) [IPBD-07-S-K](#) [IPBD-08-D-K](#) [IPBD-02-S-K](#) [IPBD-03-D-K](#) [IPBD-03-S-K](#) [IPBD-04-D-K](#)
[IPBD-04-S-K](#) [IPBD-05-S-K](#) [IPBD-07-S](#) [IPBD-08-S](#) [IPBD-09-S](#) [IPBD-10-S](#) [IPBD-02-D-K](#) [IPBD-12-D](#) [IPBD-13-D](#)
[IPBD-14-D](#) [IPBD-15-D](#) [IPBD-04-S](#) [IPBD-06-S](#) [IPBD-07-S-K-M](#) [IPBD-09-D-K](#)