



CUSTOMER DRAWING

- NOTES:
- IP67 RATED WHEN PROPERLY ASSEMBLED.
 - ALL PARTS SHIPPED ASSEMBLED.
 - PANEL THICKNESS MAX OF 0.138 [3.50].
 - MATERIALS:
RJ45 JACK: CAT5E STP
HOUSING, HEX NUT - BLACK THERMOPLASTIC
GROUND TERMINAL: NICKEL PLATED, PHOSPHER BRONZE
GASKET - BLACK, EPDM RUBBER
 - THIS PRODUCT IS RoHS COMPLIANT.

REV	ECO NUMBER	DATE	BY	APVD
A	28311	08/24/20	PC	TJK
REVISIONS				

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES [mm]
 - TWO PLACE DECIMALS ±0.02 [0.5]
 - THREE PLACE DECIMALS ±0.005 [0.13]

DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.											
SIZE	WIDTH	MULT	LBS/M	TEMPER							
FINISH					MATERIAL						
SPEC No.					SPEC No.						
FIRST USED ON				SCALE 2:1							
DATE DRAWN	BY	CHKD	APVD	Switchcraft®							
6/23/20	FM	FM	TJK	SHEET 1 OF 1							
				6/23/20				7/21/20		PART No. ENDP5EF	
				NAME RJ45 CAT 5E				REV A		PANEL MOUNT FEED-THRU JACK	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[ENDP5EF](#)