



REV.	DATE	DESCRIPTION	
NC	02/21/03	INITIAL RELEASE	




STRIPPING DIMENSIONS









NOTE:

- 1. CRIMPED FERRULE HEX CRIMP SIZE .178"
- 2. CRIMPED CONTACT PIN HEX CRIMP SIZE .068"

112568.DWG

					UN
8					INC
7	FERRULE	COPPER	NICKEL	1	
6	HEX NUT	BRASS	NICKEL	1	
5	LOCK WASHER	BRASS	NICKEL	1	
4	GASKET	RUBBER	RED	1	
3	CONTACT PIN	PHOS. BRONZE	GOLD	1	
2	INSULATOR	TEFLON	NATURAL	1	
1	BODY/HOUSING	BRASS	NICKEL	1	1.
	DESCRIPTION	MATERIAL	FINISH	QTY	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [1] ARE IN INCHES AND FOR CUSTOMER REFERANCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8 mm ± 0.20 mm 8 - 30 mm ± 0.40 mm 30 - 120 mm ± 0.50 mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:

.020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"

E :	APPROVALS	DATE	
	DRAWN G.R.S.	02/24/03	
	CHECKED		-
	ISSUED		
	SHEET 1 OF 1		
			ľ
	C:/112/112568.DWG		

Amphenol Connex

PART DESCRIPTION

BNC BULKHEAD CRIMP JACK (FOR BELDEN 8218 CABLE)

PART NO.

112568

DWG. NO.

REV. NC

SIZE A SCALE NA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

 $\frac{\text{Amphenol}}{\frac{112568}{}}$