




LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DMN	APVD		
B1		REVISED PER ECO-11-004835	11MAR11	RK	HMR		



MATERIAL: GLASS REINFORCED THERMOPLASTIC RATED 94V-0.

2. COLOR: BLUE

609-6431HD	85.95	(3.384)	64	1-1437022-3
609-5031HD	68.17	(2.684)	50	8-1437021-1
609-4031HD	55.47	(2.184)	40	5-1437021-5
609-3431HD	47.85	(1.884)	34	3-1437021-2
609-2631HD	37.69	(1.484)	26	1-1437021-2
609-2031HD	30.07	(1.184)	20	8-1437020-6
609-1631HD	24.99	(0.984)	16	6-1437020-6
609-1431HD	22.45	(0.884)	14	5-1437020-1
609-1031HD	17.37	(0.684)	10	3-1437020-7
T&B PART NO (REF)	A	NO OF POSN	PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN W. DABULAS 3/25/83	CHK: G. KLEMM 3/25/83	APVD: R.R. 3/31/83	NAME: HEAVY DUTY STRAIN RELIEF FEMALE SOCKET CONNECTOR
0. PLC ± .05	1. PLC ± .05	TE Connectivity		SIZE: A1	RESTRICTED TO: -
2. PLC ± .05	3. PLC ± .05	PRODUCT SPEC: -		WEIGHT: -	SCALE: 10:1
4. PLC ± .05	ANGLES ± .5	APPLICATION SPEC: -		CAGE CODE: 00779	DRAWING NO: 3-1437020-7
MATERIAL: -	FINISH: -	CUSTOMER DRAWING		SHEET: 1 OF 1	REV: B1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[609-2031HD](#)