

## Pneumatic contact female 3,0 mm




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 6252
Specification	Pneumatic contact female 3,0 mm
HARTING eCatalogue	<a href="https://b2b.harting.com/09140006252">https://b2b.harting.com/09140006252</a>

### Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	Without shut-off Straight

### Version

Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Limiting temperature	-40 ... +80 °C
Operating pressure	≤8 bar
Tube inner diameter	3 mm

### Material properties

Material (contacts)	Delrin acetal
Material (seal)	Buna-N
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances Not contained

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

## Commercial data

Packaging size	10
Net weight	0.7 g
Country of origin	Germany
European customs tariff number	39269097
GTIN	5713140018389
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors