

Specification	UTG2025A
Channels	2
Max.Sample Rate	200MS/s
Max.Output Frequency	25MHz
Frequency Resolution	1 μ Hz
Vertical Resolution	14 bits
Max. Arb Memory Depth	1Mpts
Waveform	Sine,Square,Ramp,Triangle,Pulse,Noise,DC,Arb
Output Amplitude Range	1mVpp~10Vpp (50 Ω) ; 2mVpp~20Vpp (High Z)
Modulation Types	AM、FM、PM、ASK、FSK、PWM、Sweep、Burst
Interface	USB Device, USB Host, LAN (UTG2062A)
General Characteristic	
Power	100-240VAC, 40-440Hz
Display	4.3 Inches 64K Color TFT LCD, 480 \times 272
Product Color	White and Gray
Product Net Weight	3.2 Kg
Product Size	231mm \times 94mm \times 283mm
Standard Accessories	BNC Cable,Power Cord , USB Cable,PC Software CD
Standard Individual Packing	Gift Box, English Manual
Standard Quantity Per Carton	2 PCs
Standard Carton Measurement	330mm \times 295mm \times 255mm
Standard Carton Cross Weight	10.5 Kg
Optional Accessories	
LAN Communication Port	