


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT * PART NO.	BUNDLE DIA.		A in. (mm)	B in. (mm)	C in. (mm)	D in. (mm)	E in. (mm)	F in. (mm)	MIN. LOOP TENSILE lbs (N)	CROSS- SECTION	WEIGHT lbs/100pcs (g)
	MIN in (mm)	MAX in (mm)									
CBR1M	.070 (1.8)	1.0 (25.4)	.038 (1.0)	.098 (2.5)	.140 (3.6)	.208 (5.3)	.195 (5.0)	4.1 (104.1)	18 (80)	MINIATURE	.061 (27.7)
CBR1.5M	.070 (1.8)	1.5 (38.1)	.042 (1.1)	.098 (2.5)	.146 (3.7)	.208 (5.3)	.209 (5.3)	5.8 (147.3)	18 (80)	MINIATURE	.084 (38.3)
CBR2M	.070 (1.8)	2.0 (50.8)	.042 (1.1)	.098 (2.5)	.146 (3.7)	.208 (5.3)	.209 (5.3)	7.3 (185.4)	18 (80)	MINIATURE	.108 (48.8)
CBR1.5I	.070 (1.8)	1.5 (38.1)	.040 (1.0)	.140 (3.6)	.180 (4.6)	.250 (6.4)	.250 (6.4)	5.9 (149.9)	40 (178)	INTERMEDIATE	.129 (58.5)
CBR3I	.070 (1.8)	3.0 (76.2)	.052 (1.3)	.140 (3.6)	.192 (4.9)	.250 (6.4)	.262 (6.7)	10.4 (264.2)	40 (178)	INTERMEDIATE	.26 (119.3)
CBR4I	.070 (1.8)	4.0 (101.6)	.052 (1.3)	.140 (3.6)	.192 (4.9)	.250 (6.4)	.262 (6.7)	13.6 (345.4)	40 (178)	INTERMEDIATE	.34 (153.2)

*SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

					TITLE		CBR SERIES CABLE TIE	
					ITEM REVISION NAME		CUSTOMER DRAWING	
							10B0150T/02	
					DATASET FILE NAME		PANDUIT	
							10B0150T_DC/02 - SS-27318_REV06	
					UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
					.x ± .01 [.25] .xxx ± .020 [.51]		NYLON 6.6	
					.xx ± .02 [.5] ANGLES ±		DRAWING NUMBER:	
							SS-27318	
					DRAWN BY		SHT 1 OF 1	
					DATE		A	
					CHK			
					SCALE			
					JABO			
					6/22/01			
					JRJR			
					NONE			

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
6	6/16/17	BWG	MPH	JADE	ADDED CBR1.5/2M TIP DESIGN VIEWS. REVISED WEBSITE NOTE. REVISED DIM. "F" FOR CBR1.5M AND CBR2M.	013188/00
5	6/18/15	BWG	MPH	JADE	CORRECTED MATERIAL NOTE.	SS-27318/05
4	11.18.14	BDK	MPH	JADE	UPDATED TITLE BORDER AND UPDATED NOTES	SS-27318

D110100DA/16