


Наименование	Сечение (мм <sup>2</sup> ) 	Форма	Размеры (мм)						
			L	L <sub>1</sub>	L <sub>2</sub>	d	d <sub>1</sub>	b	
НШП 1.5–12 (КВТ)	0.5–1.5	О	17.0	11.0	5.0	3.4	1.6	1.8	
НШП 2.5–12 (КВТ)	1.5–2.5	О	17.0	11.0	4.8	4.1	2.3	2.0	
НШП 6.0–12 (КВТ)	4–6	О	20.0	11.2	5.7	5.5	3.3	3.0	
НШП 10–12 (КВТ)	10	В	22.5	11.5	8.2	7.0	4.8	4.3	
НШП 16–13 (КВТ)	16	В	26.2	12.0	10.1	8.4	6.0	5.5	
НШП 25–15 (КВТ)	25	В	33.6	12.0	12.3	10.5	7.0	7.0	
НШП 35–20 (КВТ)	35	В	40.5	19.6	16.0	11.6	8.6	8.1	
НШП 50–20 (КВТ)	50	В	45.0	20.0	19.6	13.5	10.0	9.5	
НШП 70–25 (КВТ)	70	В	55.5	25.0	24.0	16.0	12.0	11.0	
НШП 95–25 (КВТ)	95	В	55.3	24.5	22.5	19.8	13.7	12.5	

