

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0192880179**
Status: **Active**
Overview: Application Tooling
Description: ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General


Product Family	Application Tooling
Series	207126
Comments	The Crimp Tape Module 640162000 is a base unit that will work like an applicator in a Molex TM-3000 638017200 , 638017300 industry standard crimp press or the Molex TM-4000 638017600 industry standard crimp press. The Crimp Tape Module will accept all ATP-301 and ATP-201 style crimp dies. This Crimp Tape Module will allow customers to process most of Molex's Mylar Tape product from 2 AWG uninsulated and 4 AWG insulated products and up. The Crimp Tape Module will NOT work in any other industry standard crimp press or wire process machine. These ATP-301 style die sets can be used in the older style suitcase presses.
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	<u>Application Tooling</u>
Product Name	ETC
Tool Type	Crimp Module
UPC	800753110366
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number ATP-C-530

Reference - Drawing Numbers

Application Tooling Documents
 ATS-192880179-001, ATS-TOOLING-ID-ATP, TM-192280498, TM-192280498SP, TM-640160065, TM-640160065CN, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001,



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

207126 Series

Use With

Molex Crimp Tape Module [640162000](#) used with Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex ATP-301 Press: [192280030](#) and Molex ATP-101 style presses.

Application Tooling | **FAQ**

Description | **Product #**

Avikrimp Quick Disconnect, Male, for 10-12 (5.00-3.30mm²) Wire, Mylar Tape, Tab 6.35 x 0.81mm [190250006](#)

InsulKrimp Ring Tongue Terminal for 14-16 AWG [190540093](#)

InsulKrimp Ring Tongue Terminal for Heavy Duty 14-16 AWG Wire [190540099](#)

InsulKrimp Ring Tongue Terminal for [190700120](#)

TM-640160065SP-001, TM-640160065TH-001,
TM-640160065TW-001, TM-640160065VN-001

10-12 AWG Wire,
Stud Size 6 (M3.5),
Length 27.33mm,
Mylar Tape Carrier
InsulKrimp Ring 190700122
Tongue Terminal for
10-12 AWG Wire,
Stud Size 8 (M4),
Length 27.33mm,
Mylar Tape Carrier
InsulKrimp Ring 190700125
Tongue Terminal for
10-12 AWG Wire,
Stud Size 10 (M5),
Length 27.33mm,
Mylar Tape Carrier
InsulKrimp Ring 190700131
Tongue Terminal for
10-12 AWG Wire,
Stud Size 10 (M5),
Length 31.60mm,
Mylar Tape Carrier
InsulKrimp Ring 190700133
Tongue Terminal for
10-12 AWG Wire,
Stud Size 1/4" (M6),
Length 31.60mm,
Mylar Tape Carrier
InsulKrimp Ring 190700137
Tongue Terminal for
10-12 AWG Wire,
Stud Size 5/16" (M8),
Length 31.60mm,
Mylar Tape Carrier
InsulKrimp Ring 190700144
Tongue Terminal for
10-12 AWG Wire,
Stud Size 6 (M3.5),
Length 26.21mm,
Mylar Tape Carrier
InsulKrimp Ring 190700146
Tongue Terminal for
10-12 AWG Wire,
Stud Size 8 (M4),
Length 26.21mm,
Mylar Tape Carrier
InsulKrimp Ring 190700151
Tongue Terminal for
10-12 AWG Wire,
Stud Size 1/4" (M6),
Length 34.21mm,
Mylar Tape Carrier
Avikrimp Ring 190730162
Tongue Terminal for
10 to 12 AWG Wire,
Stud Size 6 (M3.5),
Length 27.71mm,
Mylar Tape Carrier
Avikrimp Ring 190730164
Tongue Terminal for
10 to 12 AWG Wire,
Stud Size 6 (M3.5),
Expanded Flare,
Length 27.71mm,
Mylar Tape Carrier

Avikrimp Ring	<u>190730167</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 8 (M4), Length 27.71mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730169</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 8 (M4), Expanded Flare, Length 27.71mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730172</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 10 (M5), Length 27.71mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730174</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 10 (M5), Expanded Flare, Length 27.71mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730180</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 10 (M5), Length 31.95mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730184</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 10 (M5), Expanded Flare, Length 31.95mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730190</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 1/4" (M6), Length 31.95mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730194</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 1/4" (M6), Expanded Flare, Length 31.95mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730201</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 5/16" (M8), Length 31.95mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730205</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 5/16" (M8), Expanded Flare, Length 31.95mm, Mylar Tape Carrier	

Avikrimp Ring	<u>190730218</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 6 (M3.5), Length 26.59mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730224</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 8 (M4), Length 26.59mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730226</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 8 (M4), Expanded Flare, Length 26.59mm, Mylar Tape Carrier	
InsulKrimp Ring	<u>190800006</u>
Tongue Terminal for 10-12 AWG Heavy Duty Wire, Stud Size 6, 8, 10	
MULTI-STUD	<u>190810006</u>
AVIKRIMP TAPED (C-5006-MST)	
InsulKrimp Snap	<u>190990049</u>
Spade Terminal for 10-12 AWG Wire, Yellow	
InsulKrimp Snap	<u>190990051</u>
Spade for 10-12 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier, Yellow	
InsulKrimp Flanged	<u>191210048</u>
Spade Tongue Terminal for 10-12 AWG Wire, Stud Size 8 (M4), Width 8.13mm, Mylar Tape Carrier	
InsulKrimp Flanged	<u>191210054</u>
Spade Tongue Terminal for 10-12 AWG Wire, Stud Size 8 (M4), Width 9.53mm, Mylar Tape Carrier	
InsulKrimp Flanged	<u>191210057</u>
Spade Tongue Terminal for 10-12 AWG Wire, Stud Size 10 (M5), Width 9.53mm, Mylar Tape Carrier	
Avikrimp Flanged	<u>191270087</u>
Spade Tongue Terminal for 10-12 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier	
Avikrimp Flanged	<u>191270090</u>
Spade Tongue	

Terminal for 10-12 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier InsulKrimp Spade	<u>191440041</u>
Tongue Terminal for 10-12 AWG Wire, Tape and Reel InsulKrimp Spade	<u>191440043</u>
Tongue Terminal for 10-12 AWG Wire, Tape and Reel InsulKrimp Butt	<u>191540030</u>
Splice for 10-12 AWG Wire, Tape and Reel Avikrimp Hook	<u>191830020</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier Avikrimp Block	<u>191980040</u>
Spade Terminal for 10-12 AWG Wire Avikrimp Spade	<u>191980048</u>
Tongue Terminal for 12-10 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier Avikrimp Spade	<u>191980051</u>
Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier Avikrimp Wire Pin	<u>192130008</u>
Terminal for 12-10 AWG Wire, Mylar Tape Carrier	

This document was generated on 02/11/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19288-0179](#)