



300V 15A 2.5mm² 28-12AWG
 Poles: 2-24P
 Pitch: 5.0mm(.197")/5.08mm(.200")

Materials

Housing: PA66(UL 94V-0)
 Clamp: Phosphor Bronze,Nickel Plated.
 Wire Cage: Brass,Nickel Plated.
 Screw: M3,Steel A3,Zinc Plated.

序号 /Rev.No.	更改记录 /revision note	签名 /Signature	日期 /Date
-------------	---------------------	---------------	----------

设计 /Designed by	绘图 /Drawing by	审核 /Checked by	批准 /Approved by	未注公差 /General Tolerance	
				X ± 0.2	X' ± 2
				X ± 0.1	X' ± 1
				XX ± 0.05	XX' ± 0.5
				XXX ± 0.01	
备注 /Remark				单位 /Units	mm



新莱亚电子
 XINLANYA ELECTRONIC CO.,LTD