



300V 15A 24-12AWG 2.5mm²
 Poles: 2P&3P-24P
 Pitch: 5.0mm (.197")/5.08mm (.200")

Materials
 Housing: PA66 (UL 94V-0)
 Solder Pin: Brass, Tin Plated
 Wire Cage: Brass, Nickel Plated
 Screw: M2.5, Steel (A3), Zinc Plated
 Torque: 0.4N.m

序号/revno. 更改记录/revision note 签名/signature 日期/date

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	公差 General Tolerance
				X. ±0.2 X.' ±2°
图名/Title	文件编号/File No.			X. ±0.1 X.' ±1°
XYBK500-5.0				.XX ±0.05 .XX' ±0.5°
-5.08	页序/Sheet			.xxx ±0.01
备注/Remark				单位/units: mm



新莱亚电子
 XINLAIYA ELECTRONIC CO., LTD