


A 型尼龙电缆接头 A Type Nylon Cable Gland



产品信息

材料: UL 认可的尼龙 PA66
防水圈: 三元乙丙耐候橡胶
垫片(O 型圈): 三元乙丙耐候橡胶
防火等级: UL94V-2 (可定做 V0 防火等级)
保护等级: IP68
工作温度: -40°C 至 100°C
颜色种类: 黑色, 灰色, 其他颜色可定做

Product Information

Material: UL approved Nylon PA66
Hermetic Seal: Weather resistant EPDM Rubber
Washer(O Ring): Weather resistant EPDM Rubber
Fire Proof Degree: UL94V-2 (V0 customized)
Protection Degree: IP68
Working Temperature: -40°C to 100°C
Color: Black(RAL9005), Grey(RAL7035), other colors as customized

技术参数 Technical Data

螺纹规格 Thread	编号 Part No	线缆范围 Cable Range	螺纹外径 AG	螺纹长度 GL	结合长度 H	扳手尺寸 SW1/SW2
		mm	mm	mm	mm	mm
M8 x 1.25	1001M848	3-4.8	8	7.5	18	13/12
M10 x 1.5	1001M1003	1.5-3	10	8	20	15/13
M10 x 1.5	1001M1006	3-6	10	8	20	15/13
M12 x 1.5	1001M1265	3-6.5	12	9	20	18/15
M12 x 1.5	1001M1208	4-8	12	9	26	18/19
M16 x 1.5	1001M1608	4-8	16	9	26	22/19
M16 x 1.5	1001M1607	3-7	16	10	28	22/22
M16 x 1.5	1001M1610	5-10	16	10	28	22/22
M18 x 1.5	1001M1807	3-7	18	10	28	24/22
M18 x 1.5	1001M1810	5-10	18	10	28	24/22
M20 x 1.5	1001M2012	6-12	20	10.5	30	27/24
M20 x 1.5	1001M2010	5-10	20	11	34	27/27
M20 x 1.5	1001M2014	10-14	20	11	34	27/27
M22 x 1.5	1001M2210	5-10	22	11	34	29/27
M22 x 1.5	1001M2214	10-14	22	11	34	29/27
M25 x 1.5	1001M2514	10-14	25	11	34	33/27
M25 x 1.5	1001M2513	7-13	25	12	36	33/33
M25 x 1.5	1001M2518	13-18	25	12	36	33/33
M32 x 1.5	1001M3218	13-18	32	15	42	41/41
M32 x 1.5	1001M3225	18-25	32	15	42	41/41
M36 x 1.5	1001M3618	13-18	36	12	42	45/41
M36 x 1.5	1001M3625	18-25	36	12	42	45/41
M40 x 1.5	1001M4025	18-25	40	15	46	50/52
M40 x 1.5	1001M4031	22-31	40	15	46	50/52
M50 x 1.5	1001M5028	22-28	50	16	54	62/62
M50 x 1.5	1001M5041	31-41	50	16	54	62/62
M63 x 1.5	1001M6338	29-38	63	18	56	75/65
M63 x 1.5	1001M6345	35-45	63	18	56	75/65

螺纹规格 Thread	编号 Part No	线缆范围 Cable Range	螺纹外径 AG	螺纹长度 GL	结合长度 H	扳手尺寸 SW1/SW2
		mm	mm	mm	mm	mm
PG7	1001PG765	3-6.5	12.5	9	20	17/15
PG7	1001PG708	4-8	12.5	9	26	17/19
PG9	1001PG955	3-5.5	15.2	9	26	22/19
PG9	1001PG908	4-8	15.2	9	26	22/19
PG11	1001PG1107	3-7	18.6	10	28	24/22
PG11	1001PG1110	5-10	18.6	10	28	24/22
PG13.5	1001PG13.509	5-9	20.4	10.5	30	27/24
PG13.5	1001PG13.512	6-12	20.4	10.5	30	27/24
PG16	1001PG1610	5-10	22.5	11	34	30/27
PG16	1001PG1614	10-14	22.5	11	34	30/27
PG19	1001PG1910	5-10	24.0	11	34	30/27
PG19	1001PG1914	10-14	24.0	11	34	30/27
PG21	1001PG2113	7-13	28.3	12	36	36/33
PG21	1001PG2118	13-18	28.3	12	36	36/33
PG25	1001PG2520	14-20	30	12	37	37/36
PG29	1001PG2918	13-18	37	12	42	46/41
PG29	1001PG2925	18-25	37	12	42	46/41
PG36	1001PG3625	18-25	47	15	46	58/52
PG36	1001PG3631	22-31	47	15	46	58/52
PG42	1001PG4228	22-28	54	16	54	64/62
PG42	1001PG4241	31-41	54	16	54	64/62
PG48	1001PG4838	29-38	59.3	16	56	70/65
PG48	1001PG4845	35-45	59.3	16	56	70/65
螺纹规格 Thread	编号 Part No	线缆范围 Cable Range	螺纹外径 AG	螺纹长度 GL	结合长度 H	扳手尺寸 SW1/SW2
		mm	mm	mm	mm	mm
G1/4"	1001G1/465	3-6.5	13.1	8	25	18/19
G1/4"	1001G3/808	4-8	13.1	8	25	18/19
G3/8"	1001G3/807	3-7	16.6	10	28	22/22
G3/8"	1001G3/810	5-10	16.6	10	28	22/22
G1/2"	1001G1/209	5-9	20.9	10	30	27/24
G1/2"	1001G1/212	6-12	20.9	10	30	27/24
G3/4"	1001G3/413	7-13	26.4	12	38	36/33
G3/4"	1001G3/418	13-18	26.4	12	38	36/33
G1"	1001G118	13-18	33.2	17	42	46/41
G1"	1001G125	18-25	33.2	17	42	46/41
G1 1/4"	1001G1 1/425	18-25	41.9	18	46	57/52
G1 1/4"	1001G1 1/431	22-31	41.9	18	46	57/52
螺纹规格 Thread	编号 Part No	线缆范围 Cable Range	螺纹外径 AG	螺纹长度 GL	结合长度 H	扳手尺寸 SW1/SW2
		mm	mm	mm	mm	mm
NPT1/4"	1001NPT1/465	3-6.5	13.6	8	25	18/18
NPT1/4"	1001NPT1/408	4-8	13.6	8	25	18/18
NPT3/8"	1001NPT3/807	3-7	17	10	28	22/22
NPT3/8"	1001NPT3/810	5-10	17	10	28	22/22
NPT1/2"	1001NPT1/209	5-9	21.2	10	30	27/24
NPT1/2"	1001NPT1/212	6-12	21.2	10	30	27/24
NPT3/4"	1001NPT3/413	7-13	26.5	15	38	36/33
NPT3/4"	1001NPT3/418	13-18	26.5	15	38	36/33
NPT1"	1001NPT118	13-18	33.2	17	42	46/41
NPT1"	1001NPT125	18-25	33.2	17	42	46/41
NPT1 1/4"	1001NPT1 1/425	18-25	41.9	18	46	57/52
NPT1 1/4"	1001NPT1 1/431	22-31	41.9	18	46	57/52