

M12 Actuator/Sensor Distribution Boxes

ASB 4/LED | ASB 6/LED | ASB 8/LED




4-, 6-, and 8-Ports (LED)

Actuator/sensor distribution box with LED operation and function indicators, top-entry, 4-, 6-, and 8-ports, M12 sockets, 4-poles, 1 signal per socket, with integrated control cable.


– control cable is suitable for c-track applications –

4-Ports



6-Ports


Pin Assignments



M12 Actuator/Sensor Distribution Boxes

ASB 4/LED 5-4-328 | ASB 6/LED 5-4-330 | ASB/LED 8 5-4-331

8-Ports



Technical Data

Environmental Degree of protection Operating temperature range

Mechanical Housing Insert Contact

Receptacle shell O-ring

Electrical Contact resistance Voltage rating Current rating Insulation resistance

Accessories (included) ZVK ZBS IP 67 / NEMA 6P -15°C (+5°F) / +80°C (+176°F)

Distribution Boxes

TPU, self-extinguishing PA GF, self-extinguishing CuZn, pre-nickeled and 0.8 microns gold-plated CuZn, nickel-plated FKM

 $\leq 5 m \Omega$ 10-30 V DC 4 A per port / 12 A max. total > $10^9 \Omega$

2 dust covers for unused sockets 10 attachable labels

Cable Specifications

Cable No.	Outer Jacket	Conductor Size	Color	Outside Diameter
328	PUR, halogen-free	3 x 0.75 mm ² 4x 0.34 mm ²	Black	.268" (6.8 mm)
330	PUR , halogen-free	3 x 0.75 mm ² 6x 0.34 mm ²	Black	.299" (7.6 mm)
331	PUR, halogen-free	3 x 0.75 mm ² 8 x 0.34 mm ²	Black	.315" (8.0 mm)

Part Number	Ports	Standard Cable Length	Characteristics
ASB 4/LED 5-4-328/M	4	5M and 10M	
ASB 6/LED 5-4-330/M	6	5M and 10M	
ASB 8/LED 5-4-331/M	8	5M and 10M	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumberg Automation:

ASB 8/LED 5-4-331/15 M ASB 8/LED 5-4-331/20 M ASB 6/LED 5-4-330/15 M ASB 4/LED 5-4-328/10 M ASB 4/LED 5-4-328/10 M ASB 4/LED 5-4-328/5 M ASB 8/LED 5-4-331/10 M ASB 6/LED 5-4-330/5 M ASB 6/LED 5-4-330/10 M ASB 4/LED 5-4-328/5 M ASB 8/LED 5-4-331/5 M ASB 4/LED 5-4-328/20 M ASB 6/LED 5-4-330/20 M