













| | | |
|--|--|-----------------------|
| Approval | c  US  | |
| Capability | UL | IEC |
| Standard | 600V | 800V |
| Rated Voltage | 65A | 57A |
| Rated Current | Wire size | 0.2-10mm ² |
| Wire size | 20-6AWG | |
| T/W/End plate | 10.2/42.5/1.6mm | |
| Height(mm)(NS35:7.5/NS35:15/NS32) | 47/54.5/52mm | |
| Rated surge voltage/Contamination Class | 8KV/3 | |
| Stripping length | 10mm | |
| Screw thread/Tightening torque | M4/1.2N.m/10.5Lb-in | |
| Internal cylindrical gage | B6 | |
| Insulating Material/Inflammability class | PA/V-0 | |
| Specification | Model | Pieces |
| (1) Terminal block | PC 10 | 50 |
| (2) End cover  | D-PC 2.5 | 200 |
| (3) Fixed bridge | FBI 2-10 | 400 |
| 2-P | FBI 3-10 | 150 |
| 3-P | FBI 5-10 | 50 |
| 5-P | FBI 10-10 | 10 |
| 10-P | | |
| (4) Step bracket  | STL 10N/5N | 10 |
| (5) Insertion bridge | EB 2-10 | 100 |
| 2-P | EB 3-10 | 100 |
| 3-P | EB 10-10 | 10 |
| 10-P | | |
| (6) Isolator bridge bar, 10P  | ISSBI 10-10 | 10 |
| (7) Bridge bar isolator  | IS-K10 | 100 |
| (8) Switching bridge  | | |
| (9) Separating plate  | TS-K | 50 |
| (10) Separating plate, width 1.5mm  | ATP-PC | 50 |
| (11) Test plug socket  | DSB 4/7/6 | 100 |
| (12) Test plug socket insulated  | DSBJ 4/15/6 | |
| (13) Zack strip  | ZB10 | 200 |

HOW TO ORDER :

- **P** - **1** -

| | | |
|------------------|---|---|
| X | X | X |
| Customer Request | | |

Series No. No. of pole Color

| | | | | | |
|---|-------|---|--------|---|--------------|
| 1 | Gray | 4 | Green | 7 | Transp-arent |
| 2 | Blue | 5 | Orange | 8 | Yellow |
| 3 | Black | 6 | Red | 9 | White |

| | |
|---|---|
|  |  DEGSON ELECTRONICS CO., LTD. |
|  | NAME PC 10 |