



HOME > Product Info

Product Category

Product Info

1 Products

		1-1
Product No.	MSS-R-PC(40)	
HRS No.	319-0034-1 40	
Status	In Production	
RoHS	Yes	
Series	MSS	
Category	Coaxial Connectors	
No. of Positions	N/A	
Contact Mating Area Plating	Gold	
Contact Gender	Female	
Connector Type	Board mounting	
PCB Mount Type	Throughhole	
Current Rating(Amps)(Max.)	N/A	
Impedance (ohm)	50	
Frequency (GHz)(Min)	0	
Frequency (GHz)(Max)	1	
V.S.W.R. (Max)	1.2	
Termination Style	N/A	
Temperature (deg C)	-55 to 85	
Mating/Unmating Cycles	3000	
Applicable Cable	N/A	
Generic Name	N/A	
Selling Unit	1pcs.(1pcs.)	
General Description	Receptacle; Pushpull lock	
Inquiry	REQUEST	
Similar Products	Similar Products > 2 products	
e-Commerce	E-Commerce >	
Product No.	MSS-R-PC(40)	
HRS No.	319-0034-1 40	

1-1

[Terms of Service](#) [RoHS](#)



Search:



A World Leader in Electrical Connectors

[Sitemap](#)

[Contact Us](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[MSS-R-PC\(40\)](#)