

JETLINE+ SYSTEM | **GLOBAL SOLUTION OF WORKSHOP**

Create your flexible, evolutionary and innovative workspace!

Made in France

MODULAR
WORK, TIDY, SHARE AND ORGANISE

COMFORT
AN ENVIRONMENT WHERE WORKING WILL BECOME A REAL PLEASURE!


SPACE
SO MANY POSSIBILITIES TO OPTIMISE YOUR SPACE

FREEDOM
REDESIGN YOUR WORKSHOP AND CREATE YOUR IDEAL SET FREELY



LET'S DESIGN AND CREATE THE PERFECT WORKSPACE...

DOWNLOAD THE JETLINE+ 3D CONFIGURATOR (WINDOWS VERSION) from www.facom.com to create your bespoke workspace.



- FULL PRODUCTS RANGE.
- 2D VIEWING.
- 3D VIEWING.
- YOUR LIST OF PRODUCTS.



SCAN THIS QR CODE TO VISIT THE JETLINE+ MICROSITE



113AS


COMPACT ADJUSTABLE WRENCHES

ACCESSIBLE, LIGHT AND COMFORT



- Very high accessibility in confined space.
- Ergonomic handle.

113AS.C - Short adjustable wrenches



ISO 6787 NF ISO 6787 DIN 3117 ASME B107.100

- Short handle and thin profile gives optimum accessibility.
- Lightweight = Increased comfort
- Big opening for maximum versatility: up to 41mm.
- Good access to the screw = Easy setting.
- Non-protruding moving jaw at maximum capacity.
- Millimetric graduation.
- Presentation: chromed body and polished head faces.

	A	B	C x C1	E	E1	E2	E3	E4	L	L1	ΔΔ
	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[g]
113AS.6CPB	33	58	17X19	6.3	9.9	6.7	8.8	7.1	160	25.3	178
113AS.8CPB	40	74	19x23	7	12.1	8.8	10.4	9	200	32.4	328

51BS


'HIGH SAFETY' IMPACT WRENCHES



INNOVATING FASTENING SYSTEM (PATENTED)

- Work safely: no need to hold the wrench.
- Increase productivity: usable single-handed, no accessories require.

51BS - Metric safety slogging wrenches



- Patented mechanism to lock the wrench on the screw.
- No need to hold the wrench when striking=no risk of injuries, maximum security.
- Innovative & Easy to use unlock trigger.
- Hook for work at height.
- Metric sizes from 24 to 80mm.
- Presentation: black phosphate.

	A [mm]	B [mm]	E [mm]	E1 [mm]	L [mm]	ΔΔ [g]
51BS.24	24	45	19.5	32.5	180	510
51BS.27	27	45	19.5	32.5	180	493
51BS.30	30	48	21	33.8	195	607
51BS.32	32	51	21.5	34.2	195	649
51BS.36	36	59	25	37.2	205	904
51BS.41	41	62	26	37.2	231	990
51BS.46	46	71	28	39.0	240	1268
51BS.50	50	75	31	41.0	255	1493
51BS.55	55	80	35	47.5	270	1950
51BS.60	60	85	38	49.5	280	2300
51BS.65	65	93	41	48.0	300	2720
51BS.70	70	102	43	58.0	320	3490
51BS.75	75	108	48	60.0	330	3760
51BS.80	80	118	52	63.0	360	4640