

## Features

- 1/2in Rc Thread
- Stainless Steel
- Female
- Circular
- 3000lb pressure rating
- Good corrosion and heat resistance

## RS PRO Stainless Steel Coupler Male Rc 1/2in

RS Stock No.: 826-7009



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

*A 1in female RC Tapered coupler for high pressure systems with a pressure rating of up to 3000psi. Manufactured from Stainless Steel the coupling is corrosion and rust resistant and suitable for domestic and industrial applications.*

## General Specifications

Fitting Type	High Pressure
Orientation	Straight
Connection Type	Threaded
Shape	Circular
Thread Size	1/2in
Gender	Female
Thread Standard	Rc (Tapered)

## Mechanical Specifications

Length	48mm
Outer Diameter	28mm
Thread Length	10.9mm

## Operation Environment Specifications

Maximum Working Pressure Range	3000 psi (206 bar)
--------------------------------	--------------------

## Approvals

Compliance/Certifications	ASME B16.11
---------------------------	-------------

## Similar Products

RS Stock No	Thread Size (in)	Width (mm)	Outer Diameter (mm)	Thread Length (mm)
826-6992	1/4in	35	19	8.1
826-6996	3/8in	38	22	9.1
826-7009	1/2in	48	28	10.9
826-7002	3/4in	51	35	12.7
826-7006	1in	60	44	14.7
826-7015	1 1/4in	67	57	17
826-7018	1 1/2in	79	64	17.8
826-7012	2in	86	76	19