

Features

- Stainless Steel
- G1/4 (1/4in BSP)
- Inline installation
- ABS guide
- 15L/min flow rate

RS PRO Inline 1/4in Hydraulic Check Valve

RS Stock No.: 283-8295



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

A Stainless Steel inline mounting valve with a corrosion-resistant Nylon guide for increased durability.

The ball mechanism is spring-loaded for positive action, so it can be fitted vertically or horizontally and the valve has a standard CETOP (Comité Européenne des Transmissions Oléohydrauliques et Pneumatiques) mounting pattern for installation in a wide variety of hydraulic, pneumatic and mechanical applications.

The soft-seated thermoplastic ball material creates a tight seal, so it can be used with gas. For systems that use water, try an alternative component, such as a zinc-passivated carbon steel valve instead.

General Specifications

Type	Non Return Valve
Thread Size	G1/4
Body Material	316 Stainless Steel
Guide Material	Nylon
Maximum Flow Rate	15L/min
CETOP Mounting	Yes
Type of Mounting	Inline
Single/ Double	Single
Thread Size	1/4
Thread Standard	BSP
Maximum Operating Pressure	350 bar
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	+100°C