

FEATURES

- General-purpose swivel castor
- Light duty
- Load capacity of 70kg
- Wheel diameter of 75mm
- Overall height of 95mm
- Wheel width of 25mm
- Fixing plate dimensions of 75mm x 60mm
- Fixing centres of 55mm x 42mm
- Brakes not included
- Rubber tyres
- Included top plate fitting
- Four fixing holes of 6mm
- Plain bore hub bearings

RS PRO Swivel Swivel Castor, 70kg Load Capacity, 75mm Wheel Diameter

RS Stock No.: 828-6296



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

If you need a safe way to move equipment or to set up a mobile chair or desk, this 75 mm general-purpose swivel castor is ideal. It's suitable for use with light-duty transportable equipment and rotates a full 360° for maximum mobility, bearing loads of up to 70 kg.

You can attach this castor to your equipment quickly and easily thanks to its simple rectangular plate mount. Thanks to the rubber tyres, your floors are protected from marking. Whether you use it indoors or on softer outdoor surfaces, its pressed steel bracket and polypropylene hub make it durable.

General Specifications

Rotation	Swivel
Weight Class	Light Duty
Load Capacity	70kg
Tyre Material	Rubber
Hub Material	Polypropylene
Bracket Material	Pressed steel
Includes Brake	No
Features	Top Plate Fitting, Ball bearing swivel head
Applications	General Purpose, offices, warehouses and other industrial environments

Mechanical Specifications

Mounting Type	Plate
Wheel Diameter	75mm
Wheel / Tread Width	25mm
Overall Height	95mm
Number of Fixing Holes	4
Fixing Hole Size	8mm
Hub Bearing Type	Plain Bore

Fixing Centres Specifications	
Fixing Centres	55mm x 42mm
Fixing Centres (Length)	55mm
Fixing Centres (Width)	42mm

Fixing Plate Specifications	
Fixing Plate Dimensions	75mm x 60mm
Fixing Plate Length	75mm
Fixing Plate Width	60mm



Specification	
Application	General Purpose / Industrial
Features	Ball Bearing Swivel Head
Fixing Centres	55x42mm
Fixing Centres Length	55mm
Fixing Centres Width	42mm
Fixing Hole Size	8mm
Fixing Plate Dimensions	75x60mm
Fixing Plate Length	75mm
Fixing Plate Width	60mm
Hub Bearing Type	Plain
Hub Material	Polypropylene
Load Capacity	70kg
Number of Fixing Holes	4
Overall Height	95mm
Rotation	Swivel
Tyre Material	Grey Rubber Tyre
Weight Class	Light Duty
Wheel Diameter	75mm
Wheel Width	25mm