



mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		FCI		
ltr	ecn no	dr	date	linear	.X ± 0.30		projection		www.fciconnect.com		
H	T06-0074	AC	4/10/06		.XX ± 0.20		MM		title		
J	T06-0137	AC	7/18/06	angles	.XXX ± 0.10		MM		MINI USB B-TYPE SMT RECEPTACLE		
K	T06-0201	AC	12/14/06		0° ± 2°		N/A		product family 511		
L	T07-1002	JH	1/5/07	dr	JASON HSU	12/27/10	scale		code		
M	T10-0095	JH	12/27/10	enr	JASON HSU	12/27/10	A4		TWN		
N	T-004667	JH	7/27/11	chr	GARY HSIEH	12/27/10	10033526		sheet		
				appd	JOSEPH HSIA	12/27/10			1 of 2		
sheet index	revision sheet	N 1	N 2								

1 | 2

3

4

PROD NO
SEE NOTES

NOTES:

1.MATERIAL:

HOUSING: THERMOPLASTIC. UL 94V-0 RATED, COLOR: BLACK.
CONTACT: COPPER ALLOY.
SHELL: COPPER ALLOY
MYLAR: KAPTON TAPE.

2.FINISH:

CONTACT: UNDERPLATED 50u"MIN. NICKEL OVERALL
100u" MIN. MATTE TIN PLATED ON SOLDERING AREA,
SELECTIVE GOLD PLATED ON CONTACT AREA.
SHIELD: CODE N: NICKEL 40u" ~120u" PLATED OVERALL.
T: SELECTIVE 60u" MIN. MATTE TIN ON LEGS OVER 40u"~120u" NICKEL.

3.10033526-X3212XLF MEETS THE EUROPEAN UNION DIRECTIVE AS DESCRIBE
IN GS-22-008 AND ITS HSG WILL WITHSTAND EXPOSE TO 260 DEGREE C
PEAK TEMPERATURE FOR 10 SECONDS IN A IR REFLOW APPLICATION.

4. PRODUCT SPEC: GS-12-174 ; PACKAGE SPEC: GS-14-873.

5. PRODUCT ORDERING DATA :

FOR LEAD-FREE

10033526 - N X X X X M LF

LF: Lead Free

M: WITH MYLAR
BLANK: WITHOUT MYLAR

PACKAGING METHOD:
2: TAPE & REEL PACKAGING

POST OPTION:
1 : WITH PLASTIC POST.
2 : WITHOUT PLASTIC POST.

HSG MATERIAL:
1 OR 2 : HIGH TEMP THERMOPLASTIC

PLATING IN CONTACT AREA:
3 : 30u" Au.

N: NICKEL FOR SHIELD.
T: SELECTIVE TIN ON LEGS.

CONNECTOR PROFILE

RECOMMENDED PCB LAYOUT FOR 10033526-XXX1XX
GENERAL TOLERANCE +/-0.05mm

CONNECTOR PROFILE

RECOMMENDED PCB LAYOUT FOR 10033526-XXX2X
GENERAL TOLERANCE +/-0.05mm

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI www.fciconnect.com			
ltr	ecn no	dr	date	linear	projection	title			
N				.X ± 0.30		MINI USB B-TYPE SMT RECEPTACLE			
				.XX ± 0.20		product family	511	code	TWN
				.XXX ± 0.10		scale	size	dwg no	sheet
				angles	N/A	A4	10033526		
dr	JASON HSU	12/27/10							
enr	JASON HSU	12/27/10							
chr	GARY HSIEH	12/27/10							
appd	JOSEPH HSIA	12/27/10							
sheet index	revision sheet								

PDS: Rev :N

STATUS: Released

Printed: Aug 30, 2011

ACAD

1 | 2

B

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10033526-N3212LF](#) [10033526-N3212MLF](#) [10033526-N3222LF](#) [10033526-N3222MLF](#)