



Datasheet for part number DCMA-37P-F225

Our Catalog Part Number: DCMA-37P-F225
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*MA

Product Datasheet	
General	D*M High reliable D-Sub Connectors with crimp termination
Wire Gauge Range AWG	Standard: AWG 20-28. High Density: AWG 22-28
Mating Cycles	200
Contact Arrangement	37 contacts size 20
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating	7.5 A max
Contact Resistance	10 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	24 hours
Shell Material	Passivated stainless steel
Shell Finish	Stainless steel shell
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Gender	Pin
Contact Type	Crimp
Contact Material	copper alloy
Contact Finish	gold over nickel
Hardware	.120" (3,05mm) Through Hole
Disclaimer	Our facility is not currently certified by the DLA and this product is not covered by the QPL/QML.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ITT Cannon:](#)

[DCMA37PF225](#)