



M12 A-coded 4-pole, female straight connector  
for technical details see DS 21035001004



- Loading-Plan:**
- 1 — brown
  - 2 — white
  - 3 — blue
  - 4 — black

- Protection level: IP67  
- Temperature range: -25°C ... +80°C



length in "1m" step	40	XXX=400
	39	XXX=390
	.	.
	12	XXX=120
length in "0.1m" step	11	XXX=110
	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
<b>Step</b>	<b>a [m]</b>	<b>XXX</b>

4.0 to 40	+1%
0.1 to 3.9	+0.04
<b>a [m]</b>	<b>Tolerance</b>

<b>Part no.</b>	213485004XXXXX
-----------------	----------------

<b>Type of cable</b>	XX
PVC grey, 4x0.34mm <sup>2</sup>	XX=84
PUR black, 4x0.34mm <sup>2</sup>	XX=91

	All rights reserved		Created by		Inspected by		Standardisation		Date		State		
	Department EC PD - RO		POPESCUD		AVRAM		HOFFMANN		2015-12-17		Final Release		
HARTING Electronics GmbH		Title M12 A-coded Cable Assembly						Doc-Key / ECM-Nr.		Rev.		Page	
D-32339 Espelkamp		Type TB		Number 213485004XXXXX				100578831/UGD/009/B 50000098541		B		1/1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21348500484010](#)