

Specifications		
Model		UTP1306
Output voltage		0~32V
Output current		0~6A
Output power		192W
Load regulation		CV < 0.1%+5mVCC < 0.2%+3mA
Accuracy(25°C±5°C)	Voltage	< 0.1%+5mV
	Current	< 0.2%+3mA
Ripple and noise		≤1mVrms
Output regulation resolution Reliability		CV: 10mV (typical), CC: 1mA (typical); MTBF(e): ≥2000hrs
Display mode		LED voltage and current dual display
Feature		Auto conversion of constant voltage and current with current limit protection
General Characteristics		
Power		Input voltage: 110V AC/220V AC; 50Hz~60Hz
Product color		White and grey
Product net weight		1.9kg

Product size	80mm x 150mm x 230mm
Standard accessories	Power cord, output cables
Standard individual packing	Carton box, English manual
Standard quantity per carton	6pcs
Standard carton measurement	625mm x 435mm x 300mm
Standard carton gross weight	12.3kg